



DHXQFN20U: plastic dual in-line compatible thermal enhanced extremely thin quad flat package; no leads; 20 terminals; UTLP based; body 2.5 x 4.5 x 0.5 mm

SOT1045-1



DIMENSIONS (mm are the original dimensions)

| UNIT | A _{max} | A ₁ | b | D | D _h | E | E _h | e | e ₁ | L | L ₁ | v | w | y | y ₁ |
|------|------------------|----------------|--------------|------------|----------------|------------|----------------|-----|----------------|--------------|----------------|-----|------|------|----------------|
| mm | 0.5 | 0.05 0.00 | 0.30 0.18 | 4.6 4.4 | 3.35 3.05 | 2.6 2.4 | 1.35 1.05 | 0.5 | 3.5 | 0.45 0.25 | 0.13 0.05 | 0.1 | 0.05 | 0.05 | 0.1 |

| OUTLINE VERSION | REFERENCES | | | EUROPEAN PROJECTION | ISSUE DATE |
|-----------------|------------|-------|-------|---|----------------------|
| | IEC | JEDEC | JEITA | | |
| SOT1045-1 | --- | | --- |  | 07-12-01 09-08-04 |